New Generation Liquid Nitrogen Plants

CNP360 – Compact, Economic and Elegant

CNP360 arrives as a plug-and-liquify system with external compressor and chiller to lower the noise in the plant room. A fully integrated design and one button operation allows you to place CNP series liquifiers in the research labs or clean rooms. Its modular design takes a little space and allows you to extend your liquification capacity. Simply make the electrical connections and produce your own liquid nitrogen by a fully automated operation with a user friendly interface of its PLC controller. Operator only needs to replace the filters and perform routine checks between maintenance intervals of 13000 operating hours.



Production Rate ≥ 360 liter/day (≥ 384 l/day @ 23 °C)

Electrical Rating 380/400/415VAC, 3Ph, 50Hz,

480VAC, 3 Ph, 60 Hz

Power Consumption (Steady State) 42kW @ 50Hz

48kW @ 60Hz

Dimensions 1245 mm (W) x 2910 mm (L) x 1439 mm (H)

Weight 1650 kg (Empty) / 2050 kg (Full) Suggested Installation Area 4.5m (L) x 6m (W) x 3.5m (H)

Compressed Air Requirement ~42 m³/hour @ 8 bar Cooling Water Flow Rate 54 liter/min @ 4 bar

Cryocooler GM type cryocooler mounted on Dewar

Compressor He, 99.999% purity @ 245-260 psig, Water cooled

Human Machine Interface 8" Color Graphic Touch Screen

Dewar Volume 1000 liter
Operating Pressure 2.0 bar

Dewar Level Control Capacitive level sensor

Features Easy installation, fully automatic start and stop operation by PLC which

supports efficient troubleshooting, the monitor displays the operational status of the plant and the failures triggered by safety devices and sensors, single switch operation, control all components through the diagnostic screen, LN₂ transfer by one button, Automatic re-start after power failure.

Built-in Nitrogen Generator

Purity $\geq 99\%$ Dew Point up to -40°C

Flow Rate 6.4 Nm³/h @%99 N2
Ambient Temperature Range +5°C to +50°C
Maximum Altitude 3 000 meters
Noise Level <65 dB @ 1 meter

Standards CE Conformance, ISO 12100:2010, IEC60204-1, 2006/42/EC, 97/23/EC;

ISO9001:2015



Tel: 0191 477 0060 Email: info@iatt.co.uk Web: www.iatt.co.uk